



| NO. | MASSE / DIMENSION |
|-----|-------------------|
| A   | 37.4              |
| B   | 1 1/4-18NEF-2B    |
| C   | 1 3/16-18NEF-2A   |
| D   | 37.5              |
| E   | 22.0              |
| F   | 29.5              |

| NO. | BESCHREIBUNG / DESCRIPTION              |
|-----|-----------------------------------------|
| 2   | ISOLIERKÖRPER BUCHSE / INSULATOR SOCKET |
| 3   | DICHTKÖRPER / GROMMET                   |
| 4   | ENDRING / ENDRING                       |
| 6   | KONTAKTBUCHSE / CONTACT SOCKET          |
| 7   | ZYLINDERGHÄUSE / BARREL                 |
| 9   | ÜBERWURFMUTTER / COUPLING NUT           |
| 10  | DICHTRING FRONT / FRONT SEALING RING    |
| 12  | ENDGEHÄUSE / ENDBELL                    |

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| Note: Due to an automatic nomenclature system, numbers generated may not be sequential.            |
| Specification and Dimensions subject to change<br>Drawings illustrate normal insulator positioning |

|                                                                 |
|-----------------------------------------------------------------|
| Material Specification:                                         |
| Shell Material: Aluminium alloy                                 |
| Shell Plating: Olive drab chromate coating over cadmium plating |
| Insulator Material: Neoprene                                    |
| Contact Material: Copper alloy                                  |
| Contact Plating: Hard silver                                    |

|                                                                                                                                                                                                     |                                                                                                                                                  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| all dimensions are in mm<br>Dimensions without tolerance indications are general tolerances in acc. with DIN7168m                                                                                   | drawing for<br>CUSTOMER                                                                                                                          |
| <br><b>ITT</b><br><i>Engineered for life</i><br><small>ITT CANNON GmbH<br/>D - 71384 Weinstadt/Germany</small> | description <b>MS3108R20-29S</b><br><b>Plug 90°</b><br>Shortened light-weight endbell without cable clamp<br>Solder Cup / Socket / Layout: 20-29 |
| © All rights reserved. Reproduction or issue to third in any form<br>whatever is only permitted with written authorization of ITT Cannon                                                            | page 1/1<br>revision 721 12. Dec 17                                                                                                              |