




PART NUMBER
SEE TABLE


REVISION HISTORY					
REV	DOCUMENT	DESCRIPTION	CHGD BY	DATE	APPROVED
10	0106359	REDRAWN WITH CHANGE	RH	2013-12-11	M. NIRANJAN



CAT. LIST.	CIRCUIT WITH TOGGLE IN			ELECTRICAL DATA
	EXTREME POSITION KEYWAY 1-2 SIDE 4-5	CENTER	EXTREME POSITION OPPOSITE 2-3 SIDE 5-6	
I2TSI5-1	ON	OFF	ON	L312 10A 277 VAC, 20A 125 VAC 1 1/2 HP 125, 250 VAC
I2TSI5-2	OFF	NONE	ON	
I2TSI5-3	ON	NONE	ON	
(B)	NONE	OFF	ON	
I2TSI5-4	MOM OFF	NONE	ON	
I2TSI5-5	MOM ON	OFF	ON	
I2TSI5-6	MOM ON	NONE	OFF	
I2TSI5-7	MOM ON	OFF	MOM ON	
I2TSI5-8	MOM ON	NONE	ON	

LOCKWASHER LOCKING RING 2X HEX NUT

NOTES
 FURNISHED UNASSEMBLED
2 - VISUAL DIFFERENCES IN TERMINAL SHAPES AND PLATING POSSIBLE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		THIRD ANGLE PROJECTION	
DECIMAL TOL	NO PLACE --- 1 PLACE --- ±.030 2 PLACE --- ±.015 3 PLACE --- ±.005		
ANGULAR TOL -	CHAMFER -		
MATERIAL			
FINISH			
APPLICABLE DOCUMENTS: ASME Y14.100-2004 ASME Y14.5-2009			
COMPUTER GENERATED DRAWING: RASTER			

Honeywell					
TITLE SWITCH, TOGGLE					
SIZE B	CAGE CODE -	DWG NO 12TSI5 SERIES CHART 1	TYPE I	REV 10	
SCALE NONE		REF WT: .10 LBS MAX	SHEET 1 of 1		
RELEASE DATE		1972-10-28	HONEYWELL CONFIDENTIAL THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE, NOR USED FOR MANUFACTURING PURPOSE'S WITHOUT WRITTEN PERMISSION FROM HONEYWELL		
DRW: JAH		1972-08-29			
RDE: -		-			
QA: -		-			
CHK: LSD		1972-10-28			

