


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/9/12	D.GRIFFIN
B	ENC7726 UPDATE PER VENDOR SPECS	01/06/15	B.PUCHASKI

MODEL# RE1903U-	
SUFFIX	CONNECTOR TYPE
NF	N-FEMALE
NM	N-MALE
NMR	N-MALE RIGHT ANGLE
RSP	RP SMA-PLUG
RSPR	RP SMA-PLUG RIGHT ANGLE
RTP	RP TNC-PLUG
RNJ	RP N-JACK
RNP	RP N-PLUG
RTPR	RP TNC-PLUG RIGHT ANGLE
SM	SMA MALE
SMR	SMA MALE RIGHT ANGLE
TM	TNC MALE
UM	UHF-MALE
BM	BNC MALE
RBP	RP BNC PLUG
MC	MC CARD MALE
MM	MMCX MALE



4 FOOT  
COAXIAL  
PIGTAIL

Ø1.2[29]



#### NOTES:

PACKAGING:  
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE  
WITH L-COM SPECIFICATION PKG-00012

ALL DIMENSIONS FOR REFERENCE

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 [2.54] .XX = ±.01 [.25] .XXX = ±.005 [.13]  ANGULAR TOLERANCES: ALL = ± 1°  PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY B.PUCHASKI	02/08/12		
	CHECKED BY P.PESA	02/08/12	CATEGORY ANTENNA	
	APPROVED BY P.PESA	02/08/12	PRODUCT DESCRIPTION 900/1800/1900MHz 5dBi TRI-BAND OMNI ANTENNA W/ MAG BASE, 4 FOOT PIGTAIL AND CONNECTOR	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. RE1903U
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: RE1903U.SLDDRW	REV. <b>B</b>
		SHEET 1 OF 1		