





	1	2	3	4	5	6	7	8
F					REV.	ECN NO.	DATE	SIGN
E					A	Initial Release	2017/03/28	Jinhai
D					B		2017/05/12	Jinhai
C								Add Recommended thickness of plank
B								
A								




Cap	Membrane	Housing	O-Ring
-----	----------	---------	--------








Without Nut

成品料號 (Product no.)	透氣量ml/min@70mbar	主體顏色 (Body Colour)	O-Ring Color	疏水性 (Oleophobic)
VENT-PSINGY-N8001	>1000	Gray	Blue	N
VENT-PSINBK-N8001	>1000	Black	Blue	N
VENT-PSINGY-08001	>550	Gray	Black	Y
VENT-PSINBK-08001	>550	Black	Black	Y
VENT-PSINGY-08002	>1000	Gray	Green	Y
VENT-PSINBK-08002	>1000	Black	Green	Y

With Nut

成品料號 (Product no.)	透氣量ml/min@70mbar	主體顏色 (Body Colour)	O-Ring Color	疏水性 (Oleophobic)
VENT-PSIYGY-N8001	>1000	Gray	Blue	N
VENT-PSIYBK-N8001	>1000	Black	Blue	N
VENT-PSIYGY-08001	>550	Gray	Black	Y
VENT-PSIYBK-08001	>550	Black	Black	Y
VENT-PSIYGY-08002	>1000	Gray	Green	Y
VENT-PSIYBK-08002	>1000	Black	Green	Y

UNIT:mm












TITLE: M12\*1.5 VENT

TOLERANCE	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

SCALE: 2:1 SIZE: A4 SHEET 1 OF 2 REV: B WC-REV: A.4 QC: Inspection item

Amphenol LTW  
安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY	DATE
DWG NO	Jinhai	2017-05-12
VENT-PSIXXX-XXXXXX	Feng-li	2017-05-12
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2017-05-12

1	2	3	4	5	6	7	8																		
F				REV.	ECN NO.	DATE	SIGN																		
E																									
D																									
C																									
B																									
A																									
Screw Nut: Optional part No.: APTP-ABKPA012-001 螺母作為選配件																									
 <p>M12 * 1.5</p>				<table border="1"> <tr><td>REV.</td><td>ECN NO.</td><td>DATE</td><td>SIGN</td></tr> <tr><td></td><td></td><td></td><td></td></tr> <tr><td></td><td></td><td></td><td></td></tr> <tr><td></td><td></td><td></td><td></td></tr> </table>				REV.	ECN NO.	DATE	SIGN														
REV.	ECN NO.	DATE	SIGN																						
 <p>Through-hole</p> <p>11.5</p> <p>2.0~3.5</p> <p>Ø12.2 ± 0.1</p>																									
<p><u>Recommended Panel Cut-Out</u> 建議開孔尺寸</p>  <p>Threaded-hole</p> <p>14.30 ± 0.20</p> <p>6.0 ± 2</p> <p>60° ± 2</p> <p>Install</p> <p>MI2x1.5</p>				 <p>Recommended installation orientation</p> <p>建議安裝朝向</p> 																					
<p><u>Recommended Panel Cut-Out</u> 建議開孔尺寸</p>  <p>Threaded-hole</p> <p>14.30 ± 0.20</p> <p>6.0 ± 2</p> <p>60° ± 2</p> <p>Install</p> <p>MI2x1.5</p>																									
<p>UNIT:mm</p>  <p>TITLE: M12*1.5 VENT</p> <p>SCALE: 2:1</p> <p>SIZE: A4</p> <p>HEET: 2 OF 2</p> <p>TOLERANCE: ±0.25</p> <p>.XX: ±0.1</p> <p>.XXX: ±0.05</p> <p>ANGLES: ±1°</p> <p>REV. B</p> <p>WC-REV. A.4</p> <p>(QC) Inspection item</p>				<p>Note:</p> <ul style="list-style-type: none"> <li>* (QC) Important Dimension.</li> <li>* Waterproof Rate: IP68(2m, 60minutes), IP69K</li> <li>* Cap: Nylon+GF, 94V-0, UV Resistance</li> <li>* Membrane: ePTFE</li> <li>* Body: Nylon+GF, 94V-0, UV Resistance</li> <li>* O-Ring: Silicone</li> <li>* Nut Torque Force: 6.0~8.0 Kgf.cm</li> </ul> <p>Amphenol LTW 安費諾亮泰企業股份有限公司</p> <table border="1"> <tr><td>ITEM NO.</td><td>DRAWN BY</td><td>DATE</td></tr> <tr><td>VENT-PSIXXXX-XXXXXX</td><td>Jinhai</td><td>2017-05-12</td></tr> <tr><td>CUSTOMER</td><td>CHECKED BY</td><td>DATE</td></tr> <tr><td>ALTW</td><td>Feng-li</td><td>2017-05-12</td></tr> <tr><td>APPROVED BY</td><td>Jerry</td><td>DATE</td></tr> <tr><td></td><td></td><td>2017-05-12</td></tr> </table>				ITEM NO.	DRAWN BY	DATE	VENT-PSIXXXX-XXXXXX	Jinhai	2017-05-12	CUSTOMER	CHECKED BY	DATE	ALTW	Feng-li	2017-05-12	APPROVED BY	Jerry	DATE			2017-05-12
ITEM NO.	DRAWN BY	DATE																							
VENT-PSIXXXX-XXXXXX	Jinhai	2017-05-12																							
CUSTOMER	CHECKED BY	DATE																							
ALTW	Feng-li	2017-05-12																							
APPROVED BY	Jerry	DATE																							
		2017-05-12																							
	2	3	4	5	6	7	8																		