

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT INVENTORY NUMBERING SYSTEM

HSTTA 19 - 48 - Q

— PACKAGE QUANTITY: 5 = 5 pcs.
Q = 25 pcs.
TL = 250 pcs.
T = 200 pcs.
CQ = 125 pcs.
LQ = 75 pcs.
L = 50 pcs.

— LENGTH: 48 = 48" (1219mm)

— EXPANDED INSIDE DIAMETER TUBING SIZE

— ADHESIVE LINED THIN WALL HEAT SHRINK TUBING.

PANDUIT PART NUMBER	Min. Exp. I.D In. (mm)	Max. Rec. I.D In. (mm)	NOMINAL REC WALL THICKNESS In. (mm)
HSTTA19-48-Q	.187 (4.8)	.062 (1.6)	.040±.010 (1.0±.0.3)
HSTTA25-48-Q	.250 (6.4)	.080 (2.0)	.040±.010 (1.0±.0.3)
HSTTA38-48-Q	.375 (9.5)	.120 (3.0)	.055±.012 (1.4±0.3)
HSTTA50-48-5	.500 (12.7)	.160 (4.1)	.070±.014 (1.8±0.4)
HSTTA75-48-5	.750 (19.0)	.250 (6.4)	.085±.017 (2.2±0.4)
HSTTA100-48-5	1.00 (25.4)	.320 (8.1)	.100±.020 (2.5±0.5)
HSTTA150-48-5	1.50 (38.1)	.510 (12.9)	.100±.020 (2.5±0.5)

NOTES:

- SHRINK RATIO: 3:1
- SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D 'S.
- MATERIAL: POLYOLEFIN WITH ADHESIVE
- COLOR: BLACK
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE."

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239K0_PB_HSTTA_00

PANDUIT

CORP. TINLEY PARK, ILLINOIS

FLEXIBLE ADHESIVE LINED
THIN WALL HEAT SHRINK
(HSTTA)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (1.0XX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
LGRAVITT

MAT'L:

SCALE NONE

DATE
5/14/03

SEE NOTES

DRAWING NO.

GB0239K0

DWG
A
SIZE

R	5/14/03	LGG	<i>[Signature]</i>	INITIAL RELEASE	GB0239K0	R	<i>[Signature]</i>		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		