


| SHELL SIZE | "A"   | "B"   | PART NUMBER     |
|------------|-------|-------|-----------------|
| 09         | 0.701 | 0.378 | 160-000-209RY0Y |
| 15         | 1.031 | 0.378 | 160-000-215RY0Y |
| 25         | 1.571 | 0.378 | 160-000-225RY0Y |
| 37         | 2.213 | 0.378 | 160-000-237RY0Y |
| 50         | 2.114 | 0.480 | 160-000-250RY0Y |

PART NUMBER CHART



ALL VARIATIONS OF DUST CAP MEET PROTECTION LEVEL IP 50 REQUIREMENTS (DIN 40050)

**RoHS COMPLIANT**

|                  |   |                                  |                              |                          |
|------------------|---|----------------------------------|------------------------------|--------------------------|
|                  | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. |                                  | DRAWN:<br><b>PAM JENKINS</b> | DATE:<br><b>07-27-12</b> |
|                  |   |                                  | CHECKED:                     | DATE:                    |
| <h1>NorComp</h1> | SCALE:<br><b>NTS</b>  | SHEET<br><b>1</b> OF<br><b>1</b> | REV<br><b>1</b>              |                          |
|                  | DWG NO. <b>160-000-2YYRY0Y</b>  |                                  |                              |                          |