



- NOTE 1 ROTATION EXAMPLES OF REF. NO. ⑩ AND NO. ⑪ ARE SHOWN.  
 ⑫ THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑪ TO BE 3N·m.  
 LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT  
 REF. NO. ⑩ AND NO. ⑪ FROM LOOSENING.  
 3 THIS PRODUCT TO BE USED WITH CABLECLAMP, JR13WCC-\*(72).  
 \* DESIGNATE DIAMETER OF APPLICABLE CABLE.

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
5	POLYACETAL	(WHITE)			
4	DIALLYL PHTHALATE	(BLACK) UL94V-0	9	ZINC ALLOY	CHROME PLATING
3	DIALLYL PHTHALATE	(BLACK) UL94V-0	8	SILICONE RUBBER	(BLACK)
2	COPPER ALLOY	SILVER PLATING 2#m min.	7	BRASS	CHROME PLATING
1	ZINC ALLOY	CHROME PLATING	6	SILICONE RUBBER	(RED)

  

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△				
APPROVED : MO. SATOH			06. 12. 18	DRAWING NO. EDC3-111071-71		
CHECKED : EJ. KUNII			06. 12. 18	PART NO. RM15WTPZ-12P(71)		
DESIGNED : TP. KOMATSU			06. 12. 18	CODE NO. CL109-1620-6-71		
DRAWN : MK. SATO			06. 12. 15	△ 1/1		