



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/22/2018	SLI
B	ECN 9332: UPDATE CABLE NOTE	08/01/2018	SLI



"P1"
SERIES A
USB PLUG
CONTACTS: 30 μINCHES
GOLD PLATING

"P2"
SERIES B
USB PLUG
CONTACTS: 30 μINCHES
GOLD PLATING



PART NUMBER	LENGTH METERS [FEET]
U2A00016-03M	0.3 [.98]
U2A00016-05M	0.5 [1.64]
U2A00016-1M	1.0 [3.28]
U2A00016-2M	2.0 [6.56]
U2A00016-3M	3.0 [9.84]
U2A00016-5M	5.0 [16.40]

- NOTES:**
1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	APPROVALS DRAWN BY CN_Seven_Li CHECKED BY CN_Bill_Zhang APPROVED BY CN_Shawn_Pan	DATE 01/22/2018 01/22/2018 01/22/2018	50 HIGH STREET NORTH ANDOVER, MA 01845 CATEGORY USB PRODUCT DESCRIPTION CA, USB2.0 TYPE A/B LSZH W/FERRITE	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			SIZE A
	COLOR VARIATIONS MAY OCCUR			FSCM NO. 43321 DWG. NO. U2A00016 REV. B
PROJECTION 	SCALE: NONE CAD FILE: U2A00016.SLDDRW		SHEET 1 OF 1	