

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

HSTT 12 - 48 0 2

COLOR
 BLANK = BLACK 5 = GREEN
 1 = BROWN 6 = BLUE
 2 = RED 10 = WHITE
 3 = ORANGE 45 = YELLOW/GREEN
 4 = YELLOW C = CLEAR

QUANTITY PER CARTON (48 IN ONLY)
 0 = 25pcs.
 5 = 5pcs.
 2 = 2pcs.

LENGTH IN"
 INCHES FEET:
 .5 M=1000
 1 D=500
 48 T=200
 C=100
 L=50
 Q=25

TUBING SIZE - EXPANDED I.D.

TT = THIN WALL
 TTV = THIN WALL VW-1 RATED



| PANDUIT PART NUMBER | Min. Exp. I.D In. (mm) | Max. Rec. I.D In. (mm) | RECOVERED WALL In. (mm) |
|---------------------|------------------------|------------------------|-------------------------|
| HSTT05 | .046 (1.2) | .023 (.6) | .016±.003 (.406±.076) |
| HSTT06 | .063 (1.6) | .031 (.8) | .017±.003 (.432±.076) |
| HSTT09 | .093 (2.4) | .046 (1.2) | .020±.003 (.508±.076) |
| HSTT12 | .125 (3.2) | .062 (1.6) | .020±.003 (.508±.076) |
| HSTT19 | .187 (4.8) | .093 (2.4) | .020±.003 (.508±.076) |
| HSTT25 | .250 (6.4) | .125 (3.2) | .025±.003 (.635±.076) |
| HSTT38 | .375 (9.5) | .187 (4.8) | .025±.003 (.635±.076) |
| HSTT50 | .500 (12.7) | .250 (6.4) | .025±.003 (.635±.076) |
| HSTT75 | .750 (19.1) | .375 (9.5) | .030±.003 (.762±.076) |
| HSTT100 | 1.000 (25.4) | .500 (12.7) | .035±.005 (.889±.127) |
| HSTT150 | 1.500 (38.1) | .750 (19.1) | .040±.006 (1.016±.152) |
| HSTT200 | 2.000 (50.8) | 1.000 (25.4) | .045±.007 (1.143±.178) |
| HSTT300 | 3.000 (76.2) | 1.500 (38.1) | .050±.008 (1.270±.203) |
| HSTT400 | 4.000 (101.6) | 2.000 (50.8) | .055±.009 (1.397±.229) |



NOTES:

- SHRINK RATIO: 2:1
- MATERIAL: CROSSLINKED POLYOLEFIN
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"
- REELS OF PRODUCT ARE ALLOWED TO HAVE SPLICES.



| PACK CODE | M | D | T | C | L | Q |
|-----------------|---|---|---|---|---|---|
| ALLOWED SPLICES | 4 | 3 | 2 | 1 | 1 | 0 |

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|---------|-----|-----|---|----------|---|------|-----|
| 3 | 5/15/13 | LEF | VJS | ADDED NOTE #4 ALLOWED SPLICES PER REEL LENGTH | GB0239KH | 3 | RAMI | |
| 2 | 2/21/12 | LEF | | ADDED "CUSTOMER DRAWING" TO TITLE BLK REMOVED ALL TOLERANCES IN TITLE BLK | GB0239KH | 2 | RAMI | |
| 1 | 10/5/11 | LEF | | ADD COLORS 1 & 3 CHANGE METRIC (19.0 TO 19.1) | GB0239KH | 1 | RAMI | |

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597HN_DC_G00239KH_PB_HSTT_03

PANDUIT

CORP. TINLEY PARK, ILLINOIS

HSTT THIN WALL HEAT SHRINKABLE TUBING CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) _____ (.XXX) _____
 (.XX) _____ ANGLES _____

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY LGRAVITT MAT'L: SEE NOTES

DATE 5/12/03

CHK'D

SCALE NONE

DRAWING NO. GB0239KH DWG SIZE A