


DO NOT SCALE DRAWING

| REVISIONS | | | | |
|-----------|------|-------------|------------|----------|
| ZONE | REV. | DESCRIPTION | DATE | APPROVED |
| | A | DRAWN | 08-08-2013 | |



| Part No. | A |
|--------------|------|
| TRMSPS-3-01 | 4.8 |
| TRMSPS-4-01 | 6.4 |
| TRMSPS-5-01 | 7.9 |
| TRMSPS-6-01 | 9.5 |
| TRMSPS-7-01 | 11.1 |
| TRMSPS-8-01 | 12.7 |
| TRMSPS-10-01 | 15.9 |
| TRMSPS-11-01 | 17.5 |
| TRMSPS-12-01 | 19.1 |
| TRMSPS-14-01 | 22.2 |

Notes:
 1. RoHS Compliant;
 2. Top, Bottom Hole:
 $\text{Ø}4.0 \pm 0.08 \text{mm}$;
 Panel Thickness: 1.6mm;



DESIGN RIGHT. TR FASTENINGS LTD. 2003
 UNDER NO CIRCUMSTANCES MUST THIS
 DRAWING BE COPIED OR DISCLOSED.
 WITHOUT FIRST OBTAINING WRITTEN
 AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MILLIMETERS.
 SURFACE FINISH:
 TOLERANCES:
 $L \leq 4 = \pm 0.1$ $4 < L \leq 15 = \pm 0.2$
 $15 < L \leq 50 = \pm 0.3$ $50 < L \leq 100 = \pm 0.4$

| NAME | DATE |
|----------------------|------------|
| DRAWN MARTIN ELLIOTT | 08/08/2013 |
| CHK'D | |
| APP'VD | |

MATERIAL
 PA66 UL94 V2

HEAT TREATMENT
 N/A

FINISH
 NATURAL

TITLE
 MINI SUPPORT POST

CUSTOMER PART NO.

DWG NO.
 TRMSPS-XX-01

A3