


DO NOT SCALE DRAWING

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	DRAWN	08-08-2013	



Part No.	A	Fits LED
TRLEDS2E-3-01	4.8	T-1 3/4 (5mm)
TRLEDS2E-4-01	6.5	
TRLEDS2E-6-01	9.5	
TRLEDS2E-8-01	12.7	
TRLEDS2E-10-01	15.9	
TRLEDS2E-12-01	19.1	
TRLEDS2E-14-01	22.2	
TRLEDS2E-16-01	25.4	

NOTES  
Also available in flame retardant nylon(PA66 UL94V-0)



UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN MILLIMETERS.  
SURFACE FINISH:  
TOLERANCES:  
L ≤ 4 = ±0.1 4 < L ≤ 15 = ±0.2  
15 < L ≤ 50 = ±0.3 50 < L ≤ 100 = ±0.4

MATERIAL  
PA66 UL94V-2  
ROHS COMPLIANT

TITLE  
LED SPACER

NAME	DATE
DRAWN MARTIN ELLIOTT	08/08/2013
CHK'D	
APPV'D	

HEAT TREATMENT  
N/A

DESIGN RIGHT. TR FASTENINGS LTD, 2003  
UNDER NO CIRCUMSTANCES MUST THIS  
DRAWING BE COPIED OR DISCLOSED,  
WITHOUT FIRST OBTAINING WRITTEN  
AUTHORITY.

CUSTOMER PART NO.

FINISH  
NATURAL

DWG NO.  
TRLEDS2E-XX-01

A3