



POLYCARBONATE
VERSION ONLY

CUL US LISTED
FILE #E65324

TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.) Contact Factory mjm@hammondmfg.com for quotes Solid models of this enclosure available in STEP or IGES. (Part number and text placement/orientation on our products are subject to change, we do not recommend using them as a locating reference for modification purposes)

NOTE

4 cover screws, and

preformed silicone gasket.

General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)

1555S	
1555S Regular Enclosure	
General Purpose ABS RAL-7035	1555SGY
Polycarbonate RAL-7035	1555S2GY
ACCESSORIES	
Steel Inner Panels	1554RPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)	1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554RGASKET

