




SIGN	DESCRIPTION	DATE	APPROVER
△	---		
△			



Technical Data:

Electrical:

Voltage rating: 12VDC

Current rating: 5A

Contact resistance: 20mΩ

Insulation resistance: 5000MΩ / 1000V

Wire range: 22-16AWG

Mechanical:

Torque: 0.5Nm (4.4lb/in)

Operating temperature: -40°C to 105°C

Strip length: 8-9mm

 Concept Design Manufacture CIE-Group Ltd 3 Widdowson Close Blenheim Ind Est Bulwell Nottingham NG6 8WB England T: +44(0)115 9770075 F: +44(0)115 9770081 E: info@cie-group.com W: www.cie-group.com			
TOLERANCE X ±0.50 X ±0.30 X.XX ±0.20 X° ±1° 	APPROVED: Rikki So		NAME: 2.1 Female DC Jack Quick Terminal Adapter
	CHECKED: Camily Pun		
	DRAWN: Sherman Xu		
	UNIT: mm	REV.: A	
	SCALE: 4/1	PAGE: 1/1	
		PART NO: CLB-JL-8112	
		DWG NO.:	