



WIRE DIAGRAM

P1		P2
1	WHITE/ORANGE	1
2	ORANGE	2
3	WHITE/BLUE	3
6	BLUE	6

E66A06002M010

CABLE TYPE
PVC TEAL

LENGTH
M010 - 1M
M025 - 2.5M
M050 - 5M
M100 - 10M

NOTES:
MECHANICAL
RJ45
PLUG: CLEAR POLYCARBONATE
BOOT: BLACK PVC

CABLE: 24AWG 2 PAIR CONDUCTORS TEAL PVC JACKET

WRAP LABEL: MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE

ELECTRICAL:
ACCORDING TO CAT5e
VOLTAGE RATING 30V AC/DC
AMPERAGE: 1.5A

RELEASED EC NO: JGZ016-1031 DRAWN: GGUSTAFSON 2016/01/22 CHKD: MZIEL INSKI 2016/02/19 APPR: BWOODMAN 2016/02/24	DESCRIPTION REV A	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION																		
		$\nabla=0$ $\nabla=0$	<table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.13</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.25</td> <td>± ---</td> </tr> <tr> <td>0 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> </tbody> </table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.13	± ---	1 PLACE	± 0.25	± ---	0 PLACE	± ---	± ---	MM ONLY	2:1	METRIC	
			mm	INCH																					
		4 PLACES	± ---	± ---																					
3 PLACES	± ---	± ---																							
2 PLACES	± 0.13	± ---																							
1 PLACE	± 0.25	± ---																							
0 PLACE	± ---	± ---																							
	ANGULAR ± .5 °	DRAWN BY: GGUSTAFSON 2016/01/22 CHECKED BY: MZIEL INSKI 2016/02/19 APPROVED BY: BWOODMAN 2016/02/24	TITLE ENET RJ45/RJ45 2PR MALE/MALE #24AWG TEAL PVC																						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. _____ DOCUMENT NO. SD-120108-094		SHEET NO. 1 OF 1																				

SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION