

För icke direkt toleranssatta mått gäller toleransklass General tolerances if not otherwise stated		Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign																																			
		1	1016993000	4101-2143 ÄNDRAD/CHANGED 4101-2118 ÄNDRAD/CHANGED	030820	TGW																																			
<table><tr><th colspan="2">NOM DIM MM</th><th colspan="3">TOL CLASS</th></tr><tr><th>From</th><th>To</th><th>A</th><th>B</th><th>C</th></tr><tr><td>(1)</td><td>6</td><td>±0.05</td><td>±0.1</td><td>±0.2</td></tr><tr><td>(6)</td><td>30</td><td>±0.1</td><td>±0.2</td><td>±0.5</td></tr><tr><td>(30)</td><td>100</td><td>±0.15</td><td>±0.3</td><td>±0.8</td></tr><tr><td>(100)</td><td>300</td><td>±0.2</td><td>±0.5</td><td>±1.2</td></tr><tr><td>(300)</td><td>1000</td><td>±0.3</td><td>±0.8</td><td>±2</td></tr></table> Hål / Holes H13 Skarpa kanter brutna där ej annat anges. No sharp edges unless otherwise specified.		NOM DIM MM		TOL CLASS			From	To	A	B	C	(1)	6	±0.05	±0.1	±0.2	(6)	30	±0.1	±0.2	±0.5	(30)	100	±0.15	±0.3	±0.8	(100)	300	±0.2	±0.5	±1.2	(300)	1000	±0.3	±0.8	±2	MÄRKT ENLIGT RITNING 4101-2143 MARKED IN ACCORDANCE WITH DRAWING 4101-2143 1 4101-2052 0.02-10mm² 34-8 AWG 4100-3717 1 4101-2118 Embla Self-adjusting cut and strip tool Straight blade cassette 4320-0614 7 393785 00202 8				
NOM DIM MM		TOL CLASS																																							
From	To	A	B	C																																					
(1)	6	±0.05	±0.1	±0.2																																					
(6)	30	±0.1	±0.2	±0.5																																					
(30)	100	±0.15	±0.3	±0.8																																					
(100)	300	±0.2	±0.5	±1.2																																					
(300)	1000	±0.3	±0.8	±2																																					
Övriga generella toleranser enligt ritning 4100-4644. Additional general tolerances in accordance with drawing 4100-4644.																																									
Material		Behandling/Treatment			Status Fristläppt																																				
Konstr/Design JOWI	Ritad/Drawn TGW	Datum/Date 02-04-29	Skala/Scale 1:1	Kontr/Checked SE	Godk/Approved NE	Ämne/Blank																																			
pressmaster®		Benämning/Denomination Rakt blad kassette Straight blade cassette			Vikt/Veigt, gram 43200614	Art grp 012																																			
ISO 9001 REG NR FM13697					Ritn nr/Drawing no 43200614	REV 001																																			