


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	11/12/2018	BPUCHASKI



PART NUMBER	LENGTH FEET	LENGTH METERS
PPA00008-01F	1	.30
PPA00008-02F	2	.61
PPA00008-03F	3	.91
PPA00008-06F	6	1.83
PPA00008-08F	8	2.44
PPA00008-10F	10	3.05
PPA00008-15F	15	4.57
PPA00008-25F	25	7.62

NOTES:

- VOLTAGE RATING: AC ≥ 1500V/S
- CONNECTOR C19 POWER RATING: 20A UL-E257089
- CONNECTOR C20 POWER RATING: 20A UL-E257089
- CABLE: SJT 12AWGx3, 300V, 60°C VW-1 E313667 FT1
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	APPROVALS DRAWN BY BPUCHASKI CHECKED BY DFRISIELLO APPROVED BY BGATES	DATE 10/29/2018 10/29/2018 10/29/2018	50 HIGH STREET NORTH ANDOVER, MA 01845 CATEGORY POWER PRODUCTS PRODUCT DESCRIPTION SERVER/PDU POWER CORD C-20 TO C19, 20AMP
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	SIZE A FSCM NO. 43321 DWG. NO. PPA00008	
PROJECTION 	SCALE: NONE CAD FILE: PPA00008.SLDDRW		SHEET 1 OF 1