





PIN Assignment



Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm(max).
3. Insulation Resistance: DC 300V/10ms,10M ohm(MIN)

							TOLERANCE INCHES M/M					
6	A6-0000015	HDMI AM transparent dust cover	1	pcs	.X	.015	.30	TITLE: HDMI M TO DVI(24+1)F CABLE				
5	A2-R028789	HDMI AM~Black insulation~Nickel plated iron shell~PIN G/F	1	pcs	.XX	.010	.10					
4	A5-R047011	Transparent PE	10	g	.XXX	.005	.05					
3	A5-R047001	45P Black PVC RoHS	25	g	DRAWN BY			CUSTOMER :		CPC		
2	A2-R028742	DVI(24+1)F~Black insulation~Nickel plated iron shell~PIN 3u~ Before the riveting hexagonal nickel plated nut	1	pcs				CUSTOMER P/N :		CS32852		
1	A4-R002264	UL20276 (30AWG*1P+EAM)*4C+30AWG*1P+30AWG*3C+AEB(50%AL) OD:5.5MM BLACK PVC MARK:... DVI CABLE	0.2	m	CHECK BY			SCALE	NONE	DRAWING NO.:		REV. A1
NO		DESCRIPTION	Q'TY	UNIT	APPD BY			UNIT	MM			
								DATE	2019.04.09	C06026-00283		1/1