


REV	DRC26-60S**	REVISIONS			
A		SYM	DESCRIPTION	DATE	APPROVED
		NC	NEW RELEASE PER E.O. P16250	10/1/99	R.D.R.
		A	REVISED PER E.O. P19912	6/20/08	RDR



5. RECOMMENDED RETAINING BOLT TORQUE: 25-28 IN-LB [2.82-3.16Nm]

4. THIS CONNECTOR WILL ACCOMODATE THE FOLLOWING:

CONTACT SIZE	MIN. O.D.	MAX. O.D.	WIRE GAUGE RANGE
20	.040 [1.016]	.095 [2.413]	16 THRU 20 [1.00-0.50mm ²]

3. PLUG IS SUPPLIED WITH DUST CAP. (NOT SHOWN)

2. DIMENSION TOLERANCE: ±.025 [.64]

NOTES: 1. DIMENSIONS ARE IN INCHES [mm].

- 8. MATERIAL: HOUSING: PLASTIC (BLACK); BOLT: SS STEEL; CLIP: STEEL GROMMET: RUBBER
- 7. THIS PLUG MATES WITH 0944328L**-**** RECEPTACLE. (** = KEY ARRANGEMENT; **** = ALL MODIFICATIONS)
- 6. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

SIGNATURE & DATE		PLUG 60 CONTACTS SIZE 20 DRC SERIES	EP 075	MATL. CODE
DR	D. MEYER 09/10/99		3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK	[Signature] 6/20/08		DEUTSCH INDUSTRIAL	
PE	[Signature] 6/17/08		B DRC26-60S**	
APPD	D. Meyer 6/17/08	ENVELOPE	DWG SIZE	CODE 11139 SHEET OF
SCALE	NONE WT			