



Concept
Design
Manufacture

CIE-Group Ltd 3 Widdowson Close Blenheim Ind Est Bulwell Nottingham NG6 8WB England
T: +44(0)115 9770075 F: +44(0)115 9770081 E: info@cie-group.com W: www.cie-group.com

Customer:

CPC

DWG No:

20191094

REV:

Description:

-

CREATED

BY:




DATE:

LF

29/07/19

CONFIDENTIAL DOCUMENT! THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CIE-GROUP LTD. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF THE CIE-GROUP LTD IS PROHIBITED.

The cable assy should comply with the European Parliament and the Council Directive: 2011/65/EU for the restriction of hazardous substances (ROHS). The manufacturer will provide a certification proving the ROHS compliance of the cable assy whenever a customer requires this.






Terminal D-Sub

1	---	1
2	---	2
3	---	3
.	---	.
.	---	.
.	---	.
.	---	.
15	---	15
SHL	---	shell

Specification

Rating Voltage:	30VDC
Rating Current:	0.5A
Contact resistance:	30mΩ max.
Insulating resistance:	min. 100mΩ/500VDC
Operating temperature:	-40° ~ 85°C



GENERAL TOLERANCE
X.X ±0.25
X.XX ±0.15
X.XXX ±0.05
ANGLE TOLERANCE ±1°
RADIUS ±0.25
HOLE ±0.13

DESC:

DSUB Plug 90Deg 15 Pin Terminal Block

P/N:

CLB-DSUB15M-16TB-2

F/C:


51559109

DATE:

PAGE:

1 of 1

PROJECTION:



UNIT:

MM

NAME:

SIGNATURE:

APPROVED:

YES / NO