


AS VIEWED FROM FRONT MATING FACE OF CONNECTOR



EN3 RIGHT ANGLE CORD CONNECTOR - BOTH ENDS
 OVERMOLD - THERMOPLASTIC, BLACK
 CONNECTOR & COUPLING RING - THERMOPLASTIC, BLACK
 CONTACTS - COPPER ALLOY, GOLD PLATED

CA	RA	EN3	C	F	DF
CABLE ASSEMBLY	RIGHT ANGLE	CONNECTOR TYPE	CORD	GENDER	DOUBLE-ENDED FEMALE
NUMBER OF CONTACTS: 2 - (CABLE DIA. 0.215) [5.46] 3 - (CABLE DIA. 0.220) [5.59] 4 - (CABLE DIA. 0.235) [5.97] 5 - (CABLE DIA. 0.255) [6.48] 6 - (CABLE DIA. 0.275) [6.99] 8 - (CABLE DIA. 0.300) [7.62]			DIM "L" 040 (40.00 ±4.00) [1016.0 ±101.6] 079 (79.00 ± 5.00) [2006.6 ±127.0] 197 (197.00 ±10.00) [5003.8 ±254.0] 394 (394.00 ±18.50) [10007.6 ±469.9]		
PART NUMBER ORDERING CODE F - FEMALE					

CUSTOMER DRAWING

- NOTES:
1. ALL CABLE CONDUCTORS ARE 20 AWG.
 2. THESE PRODUCTS ARE RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
A	28188	07/16/19	PC	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ±0.02 [0.5]
- THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE	WIDTH	MULT	LBS/M	TEMPER					
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON					SCALE 3:2				
DATE DRAWN	BY	CHKD	APVD						
6/27/19	RDS	RDS	TJK						
			6/27/19						
NAME					PART No.				
DOUBLE ENDED EN3 OVERMOLDED CABLE ASSEMBLY					CARAEN3C_F__DF				
									REV A