




| REVISIONS | | | |
|-----------|---------------------------|----------|--------|
| REV | DESCRIPTION, ECN, EAR NO. | DATE | APP'D |
| A | PROPOSAL | OCT27/17 | L.CHAN |



- MATERIALS:**
 PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK

 CONTACTS: PHOSPHOR BRONZE
 PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES,
 SEE AMPHENOL PART NUMBER FOR DETAIL.
 50 μ" [1.27 MICRONS] MIN. NICKEL UNDERPLATE
 100 μ" [2.54 MICRONS] MIN. MATTE TIN ON CONTACT TAILS

 SHIELD: STAINLESS STEEL WITH TIN DIPPED ON PCB TAILS.
- RECOMMENDED SOLDERING TEMPERATURE:**
 WAVE SOLDERING AT 260° C MAXIMUM FOR 5 SEC MAXIMUM.
- PART NUMBER:** RJE39-888-1X00
 GOLD PLATING OPTION
 0=GOLD FLASH
 1=6u" GOLD PLATING
 2=15u" GOLD PLATING
 3=30u" GOLD PLATING
 4=50u" GOLD PLATING



| | | | | | | |
|----------------------------|------------|------------------------|--------|----------------------|----------|--|
| UNLESS SPECIFIED OTHERWISE | | DRAWN | AMY.Z | DATE | OCT27/15 | Amphenol Canada Corp. www.amphenolcanada.com |
| PRIMARY UNITS | INCH | CHECKED | L.CHAN | DATE | OCT27/15 | |
| SECONDARY UNITS | MILLIMETER | M.E. APP'D | | TITLE | | 8 PORT HIGH SPEED MODULAR JACK, 8 POSITIONS, 8 CONTACTS, SHIELDED, WITHOUT LEDs - RoHS COMPLIANT |
| REFERENCE IN PARENTHESES | | Q.A. APP'D | | DWG. NO. | | |
| GENERAL TOLERANCES | | DWG APPR. | | ENG. REL. NO. | | P-RJE39-888-1X00 |
| 1 DECIMAL PLACE | ±0.025 | REF. | | | | |
| 2 DECIMAL PLACES | ±0.020 | THIRD ANGLE PROJECTION | | DO NOT SCALE DRAWING | | REV A |
| 3 DECIMAL PLACES | ±0.015 | | | | | CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1 |
| ANGULAR DEGREES | ±1.0° | | | | | |

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.