







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECR-06-003481	28FEB2006	MF	EH
	DI	REVISED PER ECR-06-007577	03APR2006	MF	EH
	E	REVISED PER ECR-07-018671	08AUG2007	HMR	EH
	EI	REVISED PER ECR-19-020041	09JAN2020	PC	LJB

I. CIRCUIT "C" ACCEPTS:
.250 MKIII POSITIVE LOCK RECEPTACLES 63933-X, 63854-X, & 1217092-X

CIRCUITS L,G,&N ACCEPTS:
.187 MKIII POSITIVE LOCK RECEPTACLES 1217113-X, & 1217114-X



NATURAL	NYLON 66/6, V0	521781-1
COLOR	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG 19JAN2005	TE Connectivity		
DIMENSIONS: INCHES		CHK G PORTA 19JAN2005			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G PORTA 19JAN2005	NAME HOUSING, RECEPTACLE POSITIVE LOCK, 4 POSITION		
MATERIAL SEE TABLE		PRODUCT SPEC -	SIZE A200779		
FINISH SEE TABLE		APPLICATION SPEC -	DRAWING NO C-521781		
CUSTOMER DRAWING		WEIGHT -	RESTRICTED TO E		
		SCALE 3:1	SHEET OF REV		