




TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.30
.XX	±0.20
.XXX	±0.10
0.0°	±2°

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER	
ORIGINAL	①
WIRE SPECS ADDED C.B. SEP. 09/2016	②
P/N'S CREATED TO REFLECT LH & RH ASSEMBLIES C.B. NOV. 23/2016	③

**CABLE ASSY. SUPPLIED WITH BOTH CONNECTOR MATING HALVES
PRE-FITTED WITH WIRES CRIMPED TO 8.5 A. CONTACT PT. NO. 516-290-590**



**KIT CONTENTS:
SEALED POLY-BAG
520-210-002-001
520-210-002-002
MOUNTING BRACKET**

520 SERIES MATED CONNECTOR CABLE ASSEMBLY		ACAD REFERENCE NO.: 520-210-002-ASSY	
		DRAWN: F.BRIONES	DATE: FEB. 04/2013
 EDAC INC TORONTO, ONTARIO CANADA YOUR CONNECTION TO QUALITY & SERVICE		CHECKED:	DATE:
		SCALE: (IN C.A.D. 1:1)	SHEET 1 OF 1
PART NUMBER: 520-210-002-ASSY			ISSUE 1



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.