

ITEM	PART#	DESCRIPTION	QTY	UOM
A	430200400	MicroFit 3.0 Plug DR PnIMnt 4Ckt	1	PC
B	430310023	MICROFIT 3.0 M CRP TERM CHN 30AU 18AWG	4	PC
C	--	PAPER PRINTED PAPER WHITE	1	PC

FROM	TO	DESCRIPTION	COLOR
A1	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A2	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A3	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A4	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK




TABLE			
PART NUMBER	L1	L2	TITLE
2147582041	150±8	63REF	MICRO-FIT3.0 P-S 4 CIRCUIT 150MM Au
2147582042	300±10	138REF	MICRO-FIT3.0 P-S 4 CIRCUIT 300MM Au
2147582043	600±10	287REF	MICRO-FIT3.0 P-S 4 CIRCUIT 600MM Au

NOTES

1. Connector view shown is from mating side.
2. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1.39mm Max.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped on the cables.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
30/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:						
∇ = 0	mm	NTS	GENERAL TOLERANCES (UNLESS SPECIFIED)									
∇ = 0	ANGULAR TOL		±	°	EC NO: 629791							
∇ = 0	4 PLACES		±		DRWN: ARAJU		2019/12/30					
∇ = 0	3 PLACES		±		CHK'D: RDESAI01		2020/01/18					
∇ = 0	2 PLACES		±		APPR: RDESAI01		2020/01/18					
∇ = 0	1 PLACE		±		INITIAL REVISION:							
∇ = 0	0 PLACES		±		DRWN: ARAJU		2019/12/30					
∇ = 0					APPR: RDESAI01		2020/01/18					
∇ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
					A4-SIZE		214758		SEE TABLE		GENERAL MARKET	

molex		
SEE TABLE		
PRODUCT CUSTOMER DRAWING		
DOCUMENT NUMBER	DOC TYPE	DOC PART
2147582040	PSD	000
REVISION		
A		
SHEET NUMBER		1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:17
-----------------	----	--------------	------------	----------