


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN INITIAL RELEASE	02/22/2020	GUTTADAURO



NOTES
MATERIAL

- BRACKET: NICKEL SILVER ALLOY.
- KEYSTONE JACK HOUSING: ZINC ALLOY, NICKEL PLATED.
- REAR HOUSING: ZINC ALLOY, NICKEL PLATED.
- KEYSTONE JACK LATCH: PC+ABS, UL94V-0.
- CONTACT HOLDER: PC,UL94V-0.
- JACK CONTACTS: PHOSPHOR BRONZE, 50U" GOLD PAINTING.
- IDC PLASTIC: PC, UL94V-0.
- IDC TERMINALS: PHOSPHOR BRONZE, TIN OVER NICKEL UNDERCOAT.
- FACEPLATE: ZINC ALLOY.

PHYSICAL CHARACTERISTICS



- INSERTION LIFE: 750 MATING CYCLES WITH FCC COMPLIANT 8P PLUG.
- PLUG RETENTION FORCE: 11 LBF MINIMUM.
- DURABILITY: 30 TERMINATION CYCLES.
- CONTACT COMPATIBILITY: ACCOMMODATES 22 TO 24 AWG SOLID.
- OPERATING TEMPERATURE RANGE: -10°C TO + 60°C.
- STORAGE TEMPERATURE RANGE: -40°C TO +68°C.
- HUMIDITY: 10% TO 90% RH (NON-CONDENSING).

ELECTRICAL

- INSULATION RESISTANCE: 500 MΩ MINIMUM.
- DC CURRENT RATING: 1.5 Amps.
- INPUT TO OUTPUT D.C. RESISTANCE: 100 mΩ MAXIMUM.
- CONTACT RESISTANCE: 20 mΩ MAXIMUM.
- VOLTAGE PROOF (CONTACT TO CONTACT): 1000 VAC.
- VOLTAGE PROOF (CONTACT TO SHIELD): 1500 V DC.

MISCELLANEOUS

- KIT TO BE SHIPPED WITH 1X IDC CAP, 1X NYLON CABLE TIE, 1X INSTRUCTION, 2 X#4-40X1/4" LONG SCREW, 1X FLANGE ADAPTER
- ONLY ACCEPT RJ-45 8P8C PLUG.
- ACCORDING TO: ANSI/TIA-568.2-D, ISO/IEC 11801-1, IEC 60603-7
- IEEE 802.3BT POWER OVER ETHERNET PLUS PLUS(4PPOE) APPLICATION,
- IEC 60512-99-002 MATING AND UN-MATING CONNECTORS UNDER ELECTRICAL LOAD
- KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- KIT IS SHIPPED UN-ASSEMBLED



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DCUI CHECKED BY BZHANG APPROVED BY GUTTADAURO	02/19/2020 02/19/2020 02/19/2020	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION FLANGE MOUNT CAT8 SHLD KEYSTONE JACK RJ45/TL POE++	DWG. NO. ECFRJTLC8S-POE
SIZE A	CAGE CODE 43321	SCALE: NONE	CAD FILE: ECFRJTLC8S-POE.SLDDRW SHEET 1 OF 1