

**Specification:**

Dielectric Withstand  
 Max. Working Current  
 Insulation Resistance  
 Operating Temperature  
 Endurance

500V ac for 1 minute  
 1A @ 34V ac/dc  
 100MΩ @ 500V dc  
 -20° to +70°C  
 5,000 insertions

**Materials:**


Body Contact  
 Body Terminal  
 Ring Contact/Terminal  
 Tip Contact/Terminal  
 Cover/Cable Guard  
 Contact Insulator

Nickel plated Brass  
 Nickel plated Steel  
 Gold plated Phospor Bronze  
 Nickel plated Phospor Bronze  
 PE  
 PPO

**Compatible With:**  
 Schurter Plugs

4832.1300, 4832.1310 & 4832.1320

**Schematic Diagram**



ISS.	MOD. & DATE	TOLERANCES	MATL	SCALE	TITLE
1	23.11.01	XX +/- 0.4 XXX +/- 0.1 UNLESS STATED OTHERWISE	See above	2 x FULL SIZE 00 NOT SCALE DRAWING USED ON:	Line Socket, 3.5mm, 3 Pole, Insulated
		DIMS IN MM	FINISH	SHT. 1 OF 1 SHTS.	DRG No. 4832.3300
			<b>SCHURTER LTD.</b>		
			BOGNOR REGS. UNITED KINGDOM		