


PART NUMBER	TITLE	CABLE DESCRIPTION	LENGTH 'L'	CABLE COLOR
2147631211	MICROFIT 3.0 M-S 75MM 20AWG LEAD BK Au	1X20AWG DISC SR-PVC BK UL10002	75±3	BLACK
2147631212	MICROFIT 3.0 M-S 150MM 20AWG LEAD BK Au	1X20AWG DISC SR-PVC BK UL10002	150±5	BLACK
2147631213	MICROFIT 3.0 M-S 225MM 20AWG LEAD BK Au	1X20AWG DISC SR-PVC BK UL10002	225±5	BLACK
2147631214	MICROFIT 3.0 M-S 300MM 20AWG LEAD BK Au	1X20AWG DISC SR-PVC BK UL10002	300±5	BLACK
2147631215	MICROFIT 3.0 M-S 450MM 20AWG LEAD BK Au	1X20AWG DISC SR-PVC BK UL10002	450±5	BLACK
2147632211	MICROFIT 3.0 M-S 75MM 20AWG LEAD RD Au	1X20AWG DISC SR-PVC RD UL10002	75±3	RED
2147632212	MICROFIT 3.0 M-S 150MM 20AWG LEAD RD Au	1X20AWG DISC SR-PVC RD UL10002	150±5	RED
2147632213	MICROFIT 3.0 M-S 225MM 20AWG LEAD RD Au	1X20AWG DISC SR-PVC RD UL10002	225±5	RED
2147632214	MICROFIT 3.0 M-S 300MM 20AWG LEAD RD Au	1X20AWG DISC SR-PVC RD UL10002	300±5	RED
2147632215	MICROFIT 3.0 M-S 450MM 20AWG LEAD RD Au	1X20AWG DISC SR-PVC RD UL10002	450±5	RED



REVISION			
DATE	REV	DESCRIPTION	CHANGER
3/2/2020	A	INITIAL RELEASE	AS20

ITEM	PART#	DESCRIPTION	QTY	UOM
A	430310003	MicroFit 3.0 M Crp Term Chn 30Au 20-24	1	PC

Notes:

1. Crimping to be done as per Molex standards.
2. The product specification relies on the terminals & wire spec.
3. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1.2mm Max.

<b>SYMBOLS</b> DIMENSION UNITS: mm SCALE: NTS GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL: ± ° 4 PLACES: ± 3 PLACES: ± 2 PLACES: ± 1 PLACE: ± 0 PLACES: ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION CURRENT REV DESC:				
	EC NO: 637570 DRWN: AS20 2020/03/03 CHK'D: RDESAI01 2020/05/14 APPR: RDESAI01 2020/05/14				
INITIAL REVISION: DRWN: AS20 2020/03/03 APPR: RDESAI01 2020/05/14			PRODUCT CUSTOMER DRAWING		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION	DRAWING: A4-SIZE	SERIES: 214763
DOCUMENT NUMBER: 2147631211			DOC TYPE: PSD	DOC PART: 000	REVISION: A
MATERIAL NUMBER: SEE TABLE			CUSTOMER: GENERAL MARKET		SHEET NUMBER: 1 OF 1