




DIMENSIONS(mm)			
SIZE	A	B	C
15	39.50	25.00	16.30
26	48.00	33.30	24.60
44	61.50	47.05	38.40
62	77.80	63.50	54.80

NOTE:**MATERIAL**

HOUSING

FLANGE

CONTACT

SHELL

O-RING

SEALING COMPOUND

HARDWARE

PBT UL94V-0, BLACK



PBT UL94V-0, BLACK

BRASS, PLATING P/N KEY BELOW
STEEL, NICKEL

SILICONE

EPOXY

BRASS; NICKEL PLATED

HARDWARE OPTIONS**ELECTRICAL**

RATED CURRENT

3A

VOLTAGE

1000 VAC 1 MIN

INSULATOR RESISTANCE

5 GOhms MIN.

CONTACT RESISTANCE

10 mOhms MAX.

WATER PROOF

IP67

ENVIRONMENT

OPERATION TEMPERATURE

-25°C TO +85°C

HDF-VYY-213LYYY

SERIES

HDF = HD DSUB FLANGE

CONTACT TYPE

V = VERTICLE PCB MOUNT

POSITIONS

15

26

44

62

GENDER

1 = FEMALE

HARDWARE OPTIONS

01 = 4-40 THREADED INSERTS/4-40 JACKSCREWS

05 = 4-40 THREADED BOARDLOCKS/4-40 JACKSCREWS

CONTACT PLATING OPTIONS

1 = GOLD FLASH

2 = 30u" GOLD PLATING

RoHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

03/02/2020

TOLERANCES

X. ±0.40

.X ±0.30

.XX ±0.20

.XXX ±0.10

UNITS = mm

DO NOT SCALE FROM DRAWING**NorComp**

SCALE:

NTS

SHEET

1

OF

2

REV


1

DWG NO.


HDF-VYY-213LYYY

****Ø3.20MM HOLES NOT NEEDED FOR "01" HARDWARE OPTION**


15 POSITION




26 POSITION



44 POSITION



62 POSITION



RECOMMENDED PCB LAYOUT
***TYPICAL // HOLE SIZE MAY NOT BE SUITABLE FOR YOUR SPECIFIC APPLICATION**

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: J. KADEL	TOLERANCES X. ±0.40 .X ±0.30 .XX ±0.20 .XXX ±0.10	UNITS = mm NorComp	SCALE: NTS	SHEET 2	OF 2	REV 1
		DATE: 03/02/2020			DWG NO. HDF-VYY-213LYYY			