

ITEM	PART#	DESCRIPTION	QTY	UOM
A	39014063	MiniFitJrPIg SR PnlMnt V-0 6 Ckt	1	PC
B	39000124	MiniFit Term Crp Male C Bs Tin 16awg	6	PC
C	--	PAPER PRINTED PAPER WHITE	1	PC

FROM	TO	DESCRIPTION	COLOR
A1	--	1X16AWG DISC PVC BK UL1015 HOOKUP	BLACK
A2	--	1X16AWG DISC PVC BK UL1015 HOOKUP	BLACK
A3	--	1X16AWG DISC PVC BK UL1015 HOOKUP	BLACK
A4	--	1X16AWG DISC PVC BK UL1015 HOOKUP	BLACK
A5	--	1X16AWG DISC PVC BK UL1015 HOOKUP	BLACK
A6	--	1X16AWG DISC PVC BK UL1015 HOOKUP	BLACK




TABLE			
PART NUMBER	L1	L2	TITLE
2153231061	150±8	63 REF	MINIFIT JR SR M-S 6 CIRCUIT 150MM Sn
2153231062	300±10	138 REF	MINIFIT JR SR M-S 6 CIRCUIT 300MM Sn
2153231063	600±10	288 REF	MINIFIT JR SR M-S 6 CIRCUIT 600MM Sn

NOTES

1. Connector view shown is from mating side.
2. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1.8mm Max.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped in Flag type on a single cable.

MOLEX P/N
MOLEX
BATCH WK/YR
DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2020/03/23	A	INITIAL RELEASE	ARAJU

FUNCTIONAL SYMBOLS FA = 0 FE = 0 FP = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex
	DIMENSION UNITS mm	SCALE NTS	GENERAL TOLERANCES (UNLESS SPECIFIED)		
DIVISIONAL SYMBOLS	ANGULAR TOL ± °		EC NO: 638380		SEE TABLE
	4 PLACES ±	3 PLACES ±	DRWN: AS20 2020/04/06		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	PRODUCT CUSTOMER DRAWING
			A4-SIZE	215323	DOCUMENT NUMBER 2153231061
					DOC TYPE PSD
					DOC PART 000
					REVISION A
					MATERIAL NUMBER SEE TABLE
					CUSTOMER GENERAL MARKET
					SHEET NUMBER 1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2020/05/28	03:12:52
-----------------	----	--------------	------------	----------