



UNCONTROLLED DOCUMENT

NOTE:
PACKAGED IN BAGS OF 100 PIECES EACH
MAX BUNDLE DIAMETER .866 [22.0MM]
ADHESIVE TAPE ON BASE



TOLERANCES UNLESS NOTED

$\pm .005$ ON DIMENSIONS THRU $.625$
 $\pm .008$ ON DIMENSIONS $.626$ THRU 1.000
 $\pm .010$ ON DIMENSIONS 1.001 THRU 1.500
 $\pm .015$ ON DIMENSIONS LARGER THAN 1.500
 $\pm .015$ ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF		
MICRO PLASTICS INC.		
CATALOG DRAWING LADDER STYLE ADJUSTABLE CABLE CLAMP MICRO P/N NM22LCC0812 DWG. # NM22LCC0812 FILE SERVER\ENG\WEB		
MATERIAL:		6/6 NYLON
DATE	SCALE 1:2	DSB