

2011/65/EU FOR RoHS COMPLIANCY.

TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.25 .XX ±0.13 .XXX ±0.05

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.





ISSUE NUMBER ORIGINAL

NOTES:

CURRENT RATING: 2A AC/DC **VOLTAGE RATING:** 100V AC/DC **TEMPERATURE RATING:** -40°C ~ 105°C **CONTACT RESISTANCE:** $10m\Omega$ MAX. **HOUSING RESISTANCE:** $1000M\Omega$ min. WITHSTANDING VOLTAGE: 800V AC / 60s

HOUSING MATERIAL: NYLON PA66, UL94V-0





140 SERIES RIGHT ANGLE PCB MOUNT



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 140 Assembly		_
DRAWN: C.B	DATE: March 27, 2020	
CHECKED:	DATE:	_
SCALE: 5:1	SHEET 1 OF 1	_
DRAMINO NUMBER 440 Assembly		

140 Assembly **ISSUE** DRAWING NUMBER: PART NUMBER: 140-504-415-000