

ITEM	PART#	DESCRIPTION	QTY	UOM
A	334810301	MX150 ASSY 1.5 BLD 1X3 BLK A/3	1	PC
C	330001001	MX150 BLD TERM TIN 14AWG D WIND	3	PC
D	884260070	PAPER PRINTED PAPER WHITE (S100X150YAJ)	1	PC

FROM	TO	CABLE PART#	DESCRIPTION	COLOR
A1	--	100027101	14AWG DISC PVC BK OD 2.4 TXL BALAJI	BLACK
A2	--	100027101	14AWG DISC PVC BK OD 2.4 TXL BALAJI	BLACK
A3	--	100027101	14AWG DISC PVC BK OD 2.4 TXL BALAJI	BLACK




TABLE			
PART NUMBER	L1	L2	TITLE
2162831031	150±8	63 REF	MX150 P-S SR 3ckt 150mm Sn sealed cable
2162831032	300±10	138 REF	MX150 P-S SR 3ckt 300mm Sn sealed cable
2162831033	600±10	288 REF	MX150 P-S SR 3ckt 600mm Sn sealed cable

- NOTES**
1. Connector view shown is from mating side.
  2. Label text must be 2mm max. in height with Arial font.
  3. Label must be wrapped in flag type on a single cable.
  4. The free ends to be stripped twisted and tinned to the length of 5±1. the tinning dia must be 2.2mm max
  5. Sealing should pass the IP67 rating as defined by product spec.

MOLEX P/N  
MOLEX  
BATCH WK/YR  
DETAIL A

FUNCTIONAL SYMBOLS FA = 0 FE = 0 FP = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		<p>REFER THE TABLE</p> <p>PRODUCT CUSTOMER DRAWING</p>		
	DIMENSION UNITS	SCALE	EC NO: 643544				
mm	NTS	DRWN: NNANKOLA 2020/06/29					
GENERAL TOLERANCES (UNLESS SPECIFIED)		CHK'D: SD 2020/08/31					
ANGULAR TOL ± °		APPR: SD 2020/08/31		DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
4 PLACES ±		INITIAL REVISION:		2162831031	PSD	000	A
3 PLACES ±		DRWN: NNANKOLA 2020/06/29					
2 PLACES ±		APPR: SD 2020/08/31					
1 PLACE ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
0 PLACES ±		THIRD ANGLE PROJECTION					
		DRAWING					
		SERIES					
		MATERIAL NUMBER					
		CUSTOMER					
		SHEET NUMBER					
		A4-SIZE					
		216283					
		SEE TABLE					
		GENERAL MARKET					
		1 OF 1					