



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-014654	06SEP2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB


D



2320922-2
SCALE 2:1




2320922-3
SCALE 2:1




2320922-4
SCALE 2:1

C




2320922-1 SHOWN

B




SECTION A-A



SECTION A-A

- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: GREEN
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE IS 2.18 TO 3.67mm.
7. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT:
- A. 2292799-1 SMOOTH WIRE EXIT
 - B. 2292799-2 NC16/NW13 CONDUIT WIRE EXIT
 - C. 2292799-3 NC12/NW10 CONDUIT WIRE EXIT
- 90° EXIT:
- D. 2302492-1 SMOOTH WIRE EXIT
 - E. 2302492-2 NC16/NW13 CONDUIT WIRE EXIT
 - F. 2302492-3 NC12/NW10 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320915-X



SCALE 2:1

D	ORANGE	2320922-4
C	PURPLE	2320922-3
B	BLUE	2320922-2
A	TAN	2320922-1
KEY	TPA COLOR	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 28MAR2018	TE Connectivity			
DIMENSIONS:		CHK R. BALTER 28MAR2018				
mm		APVD R. BALTER 28MAR2018	NAME PLUG ASSEMBLY, 4 POSITION STD DIA SEAL, HIGH TEMP, AMPSEAL 16			
		PRODUCT SPEC 108-2184	SIZE A2			
MATERIAL		APPLICATION SPEC 114-13065	CAGE CODE -			
-		WEIGHT 12.5±1g	DRAWING NO C-2320922			
-		Customer Drawing	RESTRICTED TO -			
			SCALE 1:1			
			SHEET OF			
			REV A1			