



- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30
TO 2.54mm.
5. RECOMMENDED BACKSHELLS:

STRAIGHT EXIT
A. 2292865-1 SMOOTH WIRE EXIT
B. 2292865-2 NC20/NWI7 CONDUIT WIRE EXIT
C. 2292865-3 NCI6/NWI3 CONDUIT WIRE EXIT

90° EXIT
D. 2302486-1 SMOOTH WIRE EXIT
E. 2302486-2 NC20/NWI7 CONDUIT WIRE EXIT
F. 2302486-3 NCI6/NWI3 CONDUIT WIRE EXIT
6. RECOMMENDED SEAL PLUG: 776363-1
7. MATING CONNECTOR: 2320937-X.

D	ORANGE	23209131-4
C	PURPLE	2320931-3
B	BLUE	2320931-2
A	TAN	2320931-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±
	2 PLC ±0.30
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL	FINISH
-	-
-	-

DWN	J. MCNEAL	20MAR2018
CHK	R. BALTER	20MAR2018
APVD	R. BALTER	20MAR2018
PRODUCT SPEC	108-2184	
APPLICATION SPEC	114-13065	
WEIGHT	22.5±1g	
Customer Drawing		

TE Connectivity

NAME

CAP ASSEMBLY, 12 POSITION,
REDUCED DIA SEAL,
HIGH TEMP, AMPSEAL 16

SIZE

A2

CAGE CODE

-

DRAWING NO

C-2320931

RESTRICTED TO

-

SCALE

3:1

SHEET

1

OF

1

REV

A1