




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-016412	06SEP2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB




2320937-2
SCALE 2:1
KEY B





2320937-3
SCALE 2:1
KEY C



2320937-4
SCALE 2:1
KEY D




2320937-1 SHOWN
KEY A




SECTION A-A
SCALE 3:1

- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
7. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT:
- A. 2292802-1 SMOOTH WIRE EXIT
 - B. 2292802-2 NC20/NW17 CONDUIT WIRE EXIT
 - C. 2292802-3 NC16/NW13 CONDUIT WIRE EXIT
- 90° EXIT:
- D. 2302495-1 SMOOTH WIRE EXIT
 - E. 2302495-2 NC20/NW17 CONDUIT WIRE EXIT
 - F. 2302495-3 NC16/NW13 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320931-X.



SCALE 2:1



SCALE 2:1

D	ORANGE	2320937-4
C	PURPLE	2320937-3
B	BLUE	2320937-2
A	TAN	2320937-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J MCNEAL 06SEP2018	TE Connectivity			
		CHK R BALTER 06SEP2018				
		APVD R BALTER 06SEP2018	NAME			
DIMENSIONS:		PRODUCT SPEC	PLUG ASSEMBLY, 12 POSITION, REDUCED DIA SEAL, HIGH TEMP AMPSEAL 16			
mm		108-2184				
		APPLICATION SPEC				
		114-13065				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		20±1g	A2	-	C-2320937	-
		Customer Drawing	SCALE	1:1	SHEET	OF
						REV A1