



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-014654	06SEP2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB



- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
5. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT
- A. 2292862-1 SMOOTH WIRE EXIT
- B. 2292862-2 NC16/NW13 CONDUIT WIRE EXIT
- C. 2292862-3 NC12/NW10 CONDUIT WIRE EXIT
- 90° EXIT
- D. 2302483-1 SMOOTH WIRE EXIT
- E. 2302483-2 NC16/NW13 CONDUIT WIRE EXIT
- F. 2302483-3 NC12/NW10 CONDUIT WIRE EXIT
6. RECOMMENDED SEAL PLUG: 776363-1
7. MATING CONNECTOR: 2320934-X.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.30
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH -

MATERIAL

-

DWN J. MCNEAL 20FEB2018
CHK R. BALTER 20FEB2018
APVD R. BALTER 20FEB2018

PRODUCT SPEC

108-2184

APPLICATION SPEC

114-13065

WEIGHT

14g

Customer Drawing

TE Connectivity

NAME

CAP ASSEMBLY, 4 POSITION, REDUCED DIA SEAL, HIGH TEMP, AMPSEAL I6

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2320928

-

SCALE

3:1

SHEET

1

OF

1

REV

A1