




| REVISIONS |     |                       |           |     |      |
|-----------|-----|-----------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION           | DATE      | DWN | APVD |
|           | A   | REL PER ECO-18-015319 | 18SEP2018 | JM  | RB   |
|           | A1  | REV PER ECO-18-016694 | 18OCT2018 | JM  | RB   |
|           |     |                       |           |     |      |
|           |     |                       |           |     |      |




2320924-2  
SCALE 2:1  
KEY B




2320924-3  
SCALE 2:1  
KEY C




2320924-4  
SCALE 2:1  
KEY D



2320924-1 SHOWN  
KEY A




SECTION A-A



SECTION A-A

- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT  
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT  
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE  
COLOR: GREEN
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT  
COLOR: ORANGE
- 5 MATERIAL: SILICONE  
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE IS 2.18 TO 3.67mm.
7. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT:
- A. 2292801-1 SMOOTH WIRE EXIT
  - B. 2292801-2 NC20/NW17 CONDUIT WIRE EXIT
  - C. 2292801-3 NC16/NW13 CONDUIT WIRE EXIT
- 90° EXIT:
- D. 2302494-1 SMOOTH WIRE EXIT
  - E. 2302494-2 NC20/NW17 CONDUIT WIRE EXIT
  - F. 2302494-3 NC16/NW13 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320917-X.



SCALE 2:1

|     |           |             |
|-----|-----------|-------------|
| D   | ORANGE    | 2320924-4   |
| C   | PURPLE    | 2320924-3   |
| B   | BLUE      | 2320924-2   |
| A   | TAN       | 2320924-1   |
| KEY | TPA COLOR | PART NUMBER |

|                                        |  |                                |                                                                          |  |  |  |
|----------------------------------------|--|--------------------------------|--------------------------------------------------------------------------|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>J. MCNEAL<br>18SEP2018  | TE Connectivity                                                          |  |  |  |
| DIMENSIONS:<br>mm                      |  | CHK<br>R. BALTER<br>18SEP2018  | NAME<br>PLUG ASSEMBLY, 8 POSITION<br>STD DIA SEAL, HIGH TEMP, AMPSEAL 16 |  |  |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD<br>R. BALTER<br>18SEP2018 | SIZE<br>A2                                                               |  |  |  |
| 0 PLC ±                                |  | PRODUCT SPEC<br>108-2184       | CAGE CODE<br>-                                                           |  |  |  |
| 1 PLC ±                                |  | APPLICATION SPEC<br>114-13065  | DRAWING NO<br>C-2320924                                                  |  |  |  |
| 2 PLC ±                                |  | WEIGHT<br>16±1g                | RESTRICTED TO                                                            |  |  |  |
| 3 PLC ±                                |  | CUSTOMER DRAWING               | SCALE<br>1:1                                                             |  |  |  |
| 4 PLC ±                                |  |                                | SHEET<br>OF                                                              |  |  |  |
| ANGLES ±                               |  |                                | REV<br>A1                                                                |  |  |  |
| FINISH                                 |  |                                |                                                                          |  |  |  |