




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-014654	06SEP2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB



2320915-2
SCALE 2:1
KEY B




2320915-3
SCALE 2:1
KEY C





2320915-4
SCALE 2:1
KEY D



COMPANY LOGO



SCALE 2:1



2320915-1 SHOWN
KEY A



SECTION A-A
WITH TPA IN CLOSED POSITION

- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: GREEN
4. RECOMMENDED WIRE DIAMETER RANGE IS 2.18 TO 3.67mm.
5. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT
- A. 2292862-1 SMOOTH WIRE EXIT
- B. 2292862-2 NC16/NW13 CONDUIT WIRE EXIT
- C. 2292862-3 NC12/NW10 CONDUIT WIRE EXIT
- 90° EXIT
- D. 2302483-1 SMOOTH WIRE EXIT
- E. 2302483-2 NC16/NW13 CONDUIT WIRE EXIT
- F. 2302483-3 NC12/NW10 CONDUIT WIRE EXIT
6. RECOMMENDED SEAL PLUG: 776363-1
7. MATING CONNECTOR: 2320922-X.

D	ORANGE	2320915-4
C	PURPLE	2320915-3
B	BLUE	2320915-2
A	TAN	2320915-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±0.30
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

MATERIAL

-
-

DWN J MCNEAL 09FEB2018

CHK R BALTER 09FEB2018

APVD R BALTER 09FEB2018

PRODUCT SPEC 108-2184

APPLICATION SPEC 114-13065

WEIGHT 14g

CUSTOMER DRAWING

TE Connectivity

NAME CAP ASSEMBLY, 4 POSITION, STD DIA SEAL, HIGH TEMP, AMPSEAL 16

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A200779	C-2320915	-	-

SCALE 3:1	SHEET 1	OF 1	REV A1
-----------	---------	------	--------