




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-012662	06AUG2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB




2320913-2
SCALE 2:1
KEY B



2320913-3
SCALE 2:1
KEY C




2320913-4
SCALE 2:1
KEY D



COMPANY LOGO

SCALE 2:1



19.60

1.10 REF


18.93±0.50

2.25 REF

4.50 REF

Ø2.00 REF
2 PLC

2320913-1 SHOWN
KEY A



CAP TPA

CAP HOUSING

WIRE SEAL

CAP COVER

16.00 MAX WITH TPA
IN PRE-STAGED POSITION

47.55±0.60

SECTION A-A

1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY

2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)

3 MATERIAL: SILICONE
COLOR: MARINE BLUE

4. RECOMMENDED WIRE DIAMETER RANGE IS 2.18 TO 3.67mm.

5. RECOMMENDED BACKSHELLS:

STRAIGHT EXIT

A. 2292860-1 SMOOTH WIRE EXIT

B. 2292860-2 NC12/NW10 CONDUIT WIRE EXIT

C. 2292860-3 NC08/NW7.5 CONDUIT WIRE EXIT

90° EXIT


D. 2302481-1 SMOOTH WIRE EXIT

E. 2302481-2 NC12/NW10 CONDUIT WIRE EXIT

F. 2302481-3 NC08/NW7.5 CONDUIT WIRE EXIT

6. RECOMMENDED SEAL PLUG: 776363-1

7. MATING CONNECTOR: 2320920-X.



17.45 WITH TPA IN
CLOSED POSITION

SECTION A-A

D	ORANGE	2320913-4
C	PURPLE	2320913-3
B	BLUE	2320913-2
A	TAN	2320913-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.30
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL

-

DWN J. MCNEAL 29SEP2017

CHK R. BALTER 29SEP2017

APVD R. BALTER 29SEP2017

PRODUCT SPEC 108-2184

APPLICATION SPEC 114-13065

WEIGHT 9g

CUSTOMER DRAWING

NAME

CAP ASSEMBLY, 2 POSITION,
STD DIA SEAL, HIGH TEMP, AMPSEAL 16

SIZE A2

CAGE CODE 00779

DRAWING NO C-2320913

RESTRICTED TO

SCALE 4:1

SHEET 1

OF 1

REV A1