




REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	RELEASE	JRM 2/15/21	

ALL DIMENSIONS ARE
FOR REFERENCE ONLY
DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTEHRWISE NOTED

SPECIFICATIONS

OVERALL HEIGHT..... 7.20 [182.89]
ROTATION..... 360 DEGREES
TURN..... 360 DEGREES
TILT..... 210 DEGREES
SHIPPING WEIGHT..... 8.60 LBS
VISE OPENING..... 9 1/4 [234.95] MAXIMUM
JAW PAD WIDTH..... 1.5 [38.10]
JAW PAD HEIGHT..... 1.875 [47.63]

MATERIAL:

- VISE HEAD ASSY*..... LOW CARBON STEEL,
ZINC DIE CASTING
- BASE ASSY**..... #3 ZINC DIE CAST SILVER PAINT
- KNOB..... BLACK GLASS REINFORCED
THERMAL COMPOSITE ALLOY
- BASE CAST IRON, PAINTED BLACK
- JAW PADS..... BLACK NEOPRENE
- BUMPON..... BLACK RUBBER
- SCREW..... 1/4-20 X 1/2 PHILLIPS HEAD, STEEL

*VISE HEAD ASSEMBLY INCLUDES ADJUSTING SCREW, GUIDE ROD, GUIDE
BLOCKS AND CRANK HANDLE.
**BASE ASSEMBLY INCLUDES HALF BALL HOUSINGS, RETAINER RING,
SCREWS, STUD AND NUT.

		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL± 1/64 ANGULAR: MACH±1/2° BEND ± TWO PLACE DECIMAL: ±.01 THREE PLACE DECIMAL: ±.005	DRAWN	NAME	DATE	 7540 Colbert Drive, Reno, Nevada 89511-1225 Phone (775) 850-2900 Fax (775) 850-2929 TITLE: PORTABLE MULTI-PRUPOSE VISE SPEC SHEET
			CHECKED			
			ENG APPR.			
			MFG APPR.			
			Q.A.			
		INTERPRET GEOMETRIC TOLERANCING PER: ASME 14.5M -2009 MATERIAL	COMMENTS:			SIZE DWG. NO. REV B334-SPA
NEXT ASSY	USED ON	FINISH				
APPLICATION		DO NOT SCALE DRAWING	SCALE: 1:2 WEIGHT: SHEET 1 OF 1			

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
PANAVISE PRODUCTS INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
PANAVISE PRODUCTS INC IS
PROHIBITED.