








P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	Correct Title	15AUG2019	AL	HL
	4	SOLDER AREA GOLD FLASH	12OCT2019	AL	HL
	5	ADD NEW PARTS	20JULY2020	A.L	H.L
	A	FORMAL RELEASE	13OCT2020	A.L	H.L

NOTES:


1. MATERIAL
HOUSING :HIGH TEMP THERMO PLASTIC UL94V-0
CONTACT :COPPER ALLOY
SOLDER PEG : COPPER ALLOY
- 2 FINISH
UNDERPLATED : 1.27um MIN.NICKEL ALL OVER
CONTACT MATING AREA : MEETS THE PERFORMANCE REQUIREMENTS
OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-32658.
SOLDER AREA : GOLD FLASH



SECTION S-S
SCALE 10:1
(SIGNAL CONTACTS)



ALL CONTACTS




SECTION G-G
SCALE 10:1
(GROUND CONTACTS)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC 108-32658 APPLICATION SPEC 114-115003 WEIGHT -	11JUN2019 10OCT2019 10OCT2019	TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT			
MATERIAL -		FINISH -		SIZE A200779	CAGE CODE C-2357739	DRAWING NO -	RESTRICTED TO -
SEE NOTE 1		SEE NOTE 2		CUSTOMER DRAWING		SCALE 1:1	SHEET OF 5 REV A

TAPE & REEL	WITH	2357739-3
HARD TRAY	WITH	2357739-2
HARD TRAY	WITHOUT	2357739-1
PACKAGE	CAP	P/N

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



REFERENCE P.C. BOARD LAYOUT



G: Ground

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 11JUN2019	TE Connectivity		
DIMENSIONS: mm		CHK HOPE LU 10OCT2019			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HOPE LU 10OCT2019	NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT		
		PRODUCT SPEC 108-32658			
		APPLICATION SPEC 114-115003	SIZE A2	CAGE CODE 00779	DRAWING NO C-2357739
MATERIAL -	FINISH -	WEIGHT -	RESTRICTED TO -		
SEE NOTE 1		SEE NOTE 2	CUSTOMER DRAWING		
			SCALE 1:1	SHEET 2 OF 5	REV A


WITHOUT PICK UP CAP
2357739-1

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




SECT. D-D
(SCALE 2:1)
(CONNECTOR NOT SECTION)




DETAIL C
(SCALE 2:1)



E-E
(SCALE 2:1)






THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC 108-32658 APPLICATION SPEC 114-115003 WEIGHT -	11JUN2019 10OCT2019 10OCT2019	TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.05 4 PLC ±0.0250 ANGLES ±3°				
MATERIAL -	FINISH -			NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT	RESTRICTED TO -
SEE NOTE 1	SEE NOTE 2	CUSTOMER DRAWING	SCALE 1:1	SHEET 3 OF 5	REV A



P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


DIRECTION OFF TOP OF REEL

REEL WITH PICK UP CAP
2357739-3




(4.25)

CONNECTOR DETAIL



SEE DETAIL F

WEEDING THE COVER TAPE
AROUND THE OUTER
PERIPHERY IN
A TURN.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC 108-32658 APPLICATION SPEC 114-115003 WEIGHT -	11JUN2019 10OCT2019 10OCT2019	TE TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 1 PLC ± 0.3 2 PLC ± 0.15 3 PLC ± 0.05 4 PLC ± 0.0250 ANGLES $\pm 3^\circ$ FINISH -	NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT	SIZE A2	CAGE CODE 00779	DRAWING NO C-2357739
MATERIAL - SEE NOTE 1	SEE NOTE 2	CUSTOMER DRAWING	SCALE 1:1	SHEET 5 OF 5	REV A