








1. RJ45 In-Line Coupler:
PC/ABS, UL 94V-0, Black colour
2. RJ45 In-Line Coupler Contact:
Phosphor Bronze, 3-50 micro inches
gold plating over nickel plate.
3. PCB: FR4, UL 94V-0
4. Frame: Polyamide UL94V-2

PART NO.	COLOUR	FIXING HOLE DETAILS
CP30220S	BLACK	HOLE Ø3.5 x CSK 82° x Ø5.85
CP30220SW	WHITE	
CP30220SX	BLACK	PLAIN HOLE Ø2.50
CP30220SXW	WHITE	

1. T568A & T568B wiring.
2. Meet ISO/IEC 11801 and EN50173
4. Meet ANSI/TIA/EIA 568B.2
5. Operating Temperatures: Min -10°C Max +70°C



RoHS
✓ COMPLIANT

TOLERANCE

NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±
HOLE Ø ±
ANGLES ±
UNLESS
OTHERWISE STATE

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION: 

DO NOT SCALE

MATERIAL:	SEE NOTES + TABLE
-----------	-------------------

TITLE: FEED THROUGH FTP CAT5e RJ45 SHIELDED

FINISH: SEE NOTES + TABLE

DRWG. No.	CP30220S
-----------	----------

DRAWN: D.P.J.

APPROVED: D.P.J.

DRWG. No.

FORM: A4DRWGH

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2015