

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2157591005](#)
Status: **Active**
Overview: [Micro-Fit+ Connector System](#)
Description: Micro-Fit+ Receptacle Housing, Single Row, 5 Circuits, UL 94V-0, Glow-Wire Capable, Black

Documents:

[Drawing \(PDF\)](#)
[Product Specification 2064600000-PS-000 \(PDF\)](#)
[Packaging Specification 2157590003-PK-000 \(PDF\)](#)
[Test Summary 2157590005-TS-000 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Housings
Series [215759](#)
Application Power, Wire-to-Board
Overview [Micro-Fit+ Connector System](#)
Product Name Micro-Fit+
UPC 193264921614

Physical

Circuits (maximum) 5
Color - Resin Black
Gender Receptacle
Glow-Wire Capable Yes
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 0.672/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.00mm
Pitch - Termination Interface 3.00mm
Polarized to Mating Part Yes
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification 2157590003-PK-000
Product Specification 2064600000-PS-000
Sales Drawing 2157590002-000
Test Summary 2157590005-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[215759](#) Series

Mates With

Micro-Fit+ Headers [216571](#) , [215760](#)