

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2157591006

Status:

Active

Overview:

Micro-Fit+ Connector System

Description:

Micro-Fit+ Receptacle Housing, Single Row, 6 Circuits, UL 94V-0, Glow-Wire Capable, Black



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[Product Specification 2064600000-PS-000 \(PDF\)](#)

[Packaging Specification 2157590003-PK-000 \(PDF\)](#)

[Test Summary 2157590005-TS-000 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Housings
Series	215759
Application	Power, Wire-to-Board
Overview	Micro-Fit+ Connector System
Product Name	Micro-Fit+
UPC	193264921638
Physical	
Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.780/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2157590003-PK-000
Product Specification	2064600000-PS-000
Sales Drawing	2157590002-000
Test Summary	2157590005-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215759 Series

Mates With

Micro-Fit+ Headers [216571](#) , [215760](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION