

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2177911124](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Squba 1.8 Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series [217791](#)
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Squba Crimp Terminals
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name Squba
UPC 195842124257

Physical
Cable Length 300.00mm
Circuits (Loaded) 1
Color - Resin Black
Gender Female-Pigtail
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin PVC
Net Weight 1.380/g
Number of Rows 1
Packaging Type Bag
Single Ended Yes
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.95mm-1.40mm
Wire Size AWG 22
Wire/Cable Type UL 10002

Electrical
Current - Maximum per Contact 6.0A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers
Sales Drawing 2177911121-000

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[217791](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION