

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2177911101

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Squba 1.8 Female-to-Pigtail, Tin (Sn) Plating, 75.00mm Length, 24 AWG, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	217791
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Squba Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Squba
UPC	195842124172
Physical	
Cable Length	75.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	0.289/g
Number of Rows	1
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.95mm-1.40mm
Wire Size AWG	24
Wire/Cable Type	UL 10002
Electrical	
Current - Maximum per Contact	6.0A
Voltage - Maximum	125V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2177911101-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

217791 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION