

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2177902124](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Squba 1.8 Female-to-Squba 1.8 Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Red



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series [217790](#)
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Squba Crimp Terminals
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name Squba
UPC 195842124158

Physical
Cable Length 300.00mm
Circuits (Loaded) 1
Color - Resin Red
Gender Female-Female
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin PVC
Net Weight 1.529/g
Number of Rows 1
Packaging Type Bag
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.95mm-1.40mm
Wire Size AWG 22
Wire/Cable Type UL 10002

Electrical
Current - Maximum per Contact 6.0A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers
Sales Drawing 2177901121-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[217790](#) Series