

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	10APR2017	DW	CW

WIRE RANGE

M20X 1.5

(24.5)

7

22

Ø24.5

NOTES / 注解:

I. TECHNICAL CHARACTERISTICS / 技术参数:

SHELL MATERIAL / 主体材料: NICKEL PLATED BRASS / 铜镀镍

SEAL MATERIAL / 密封材料: RUBBER, BLACK

PINCH RING MATERIAL / 夹紧件材料: NYLON, GREY

OPERATION TEMPERATURE / 工作温度: -40°C - +100°C

PROTECTION DEGREE / 防护等级: IP68

WIRE RANGE / 夹线范围: 7-12 mm

T3706200103-000

DLX-20-MC (7-12)
电磁屏蔽金属接头 M20 (7-12)PART NUMBER
料号PART DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

FINISH

DWN 10APR2017

DAVID WANG

CHK 10APR2017

CHRIS WANG

APVD 10APR2017

XIANG XU

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME
DLX-20-MC (7~12)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-T3706200103000

SCALE
2:1SHEET
1 OF 1REV
A

1470-19 (3/13)