

printed on 10 May 2021 13:57 (China Standard Time) from IE236667

D

C

B

A

D





C

B

A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	10JUN2015	GY	CW
	A1	ECR-18-009564	25SEP2018	CD	CW
	B	ECR-20-012069	08MAY2021	BS	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数：
壳体材料： 铝合金
表面处理： 见表格
防护等级： IP68 （配合）

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10JUN2015 Gino.Yao	TE Connectivity			
DIMENSIONS:		CHK 10JUN2015 Chris.Wang				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 10JUN2015 Xiang.Xu	NAME H10BPR-TSHC-PG/M			
	0 PLC	±-	PRODUCT SPEC 108-137014			
	1 PLC	±-	APPLICATION SPEC 114-137014			
	2 PLC	±-	WEIGHT -			
	3 PLC	±-	Customer Drawing			
MATERIAL		FINISH	SIZE A2	CAGE CODE -	DRAWING NO. T191210XXXXX00	RESTRICTED TO -
			SCALE 1:1		SHEET 1 OF 2	REV B

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTE :
SEE SHEET 1
备注 :
见 SHEET 1

T1912102125-001	POWDER COATED, DEEP GREY 粉末喷涂, 深灰色	H10BPR-TSHC-M25	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,DEEP GREY,NO LOGO H10BPR上壳,中部锁定,侧出M25,深灰色粉末喷涂,无LOGO	M25	TYPE2 类型2
T1912102132-001	POWDER COATED, DEEP GREY 粉末喷涂, 深灰色	H10BPR-TSHC-M32	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M32,POWDER COATED,DEEP GREY,NO LOGO H10BPR上壳,中部锁定,侧出M32,深灰色粉末喷涂,无LOGO	M32	
T1912102132-000	POWDER COATED, GREY 粉末喷涂, 灰色	H10BPR-TSHC-M32	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M32,POWDER COATED,GREY H10BPR上壳,中部锁定,侧出M32,灰色粉末喷涂	M32	TYPE1 类型1
T1912102129-000	POWDER COATED, GREY 粉末喷涂, 灰色	H10BPR-TSHC-PG29	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG29,POWDER COATED,GREY H10BPR上壳,中部锁定,侧出PG29,灰色粉末喷涂	PG29	
T1912102125-000	POWDER COATED, GREY 粉末喷涂, 灰色	H10BPR-TSHC-M25	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,GREY H10BPR上壳,中部锁定,侧出M25,灰色粉末喷涂	M25	
T1912102121-000	POWDER COATED, GREY 粉末喷涂, 灰色	H10BPR-TSHC-PG21	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,GREY H10BPR上壳,中部锁定,侧出PG21,灰色粉末喷涂	PG21	
T1912102120-000	POWDER COATED, GREY 粉末喷涂, 灰色	H10BPR-TSHC-M20	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,GREY H10BPR上壳,中部锁定,侧出M20,灰色粉末喷涂	M20	
T1912102116-000	POWDER COATED, GREY 粉末喷涂, 灰色	H10BPR-TSHC-PG16	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,GREY H10BPR上壳,中部锁定,侧出PG16,灰色粉末喷涂	PG16	
T1912101132-000	POWDER COATED,SILVER WHITE 粉末喷涂, 银白色	H10BPR-TSHC-M32	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M32,POWDER COATED,SILVER WHITE H10BPR上壳,中部锁定,侧出M32,银白色粉末喷涂	M32	
T1912101129-000	POWDER COATED,SILVER WHITE 粉末喷涂, 银白色	H10BPR-TSHC-PG29	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG29,POWDER COATED,SILVER WHITE H10BPR上壳,中部锁定,侧出PG29,银白色粉末喷涂	PG29	
T1912101125-000	POWDER COATED,SILVER WHITE 粉末喷涂, 银白色	H10BPR-TSHC-M25	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,SILVER WHITE H10BPR上壳,中部锁定,侧出M25,银白色粉末喷涂	M25	
T1912101121-000	POWDER COATED,SILVER WHITE 粉末喷涂, 银白色	H10BPR-TSHC-PG21	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,SILVER WHITE H10BPR上壳,中部锁定,侧出PG21,银白色粉末喷涂	PG21	
T1912101120-000	POWDER COATED,SILVER WHITE 粉末喷涂, 银白色	H10BPR-TSHC-M20	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,SILVER WHITE H10BPR上壳,中部锁定,侧出M20,银白色粉末喷涂	M20	
T1912101116-000	POWDER COATED,SILVER WHITE 粉末喷涂, 银白色	H10BPR-TSHC-PG16	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,SILVER WHITE H10BPR上壳,中部锁定,侧出PG16,银白色粉末喷涂	PG16	
T1912100132-000	POWDER COATED,BLACK 粉末喷涂, 黑色	H10BPR-TSHC-M32	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M32,POWDER COATED,BLACK H10BPR上壳,中部锁定,侧出M32,黑色粉末喷涂	M32	
T1912100129-000	POWDER COATED,BLACK 粉末喷涂, 黑色	H10BPR-TSHC-PG29	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG29,POWDER COATED,BLACK H10BPR上壳,中部锁定,侧出PG29,黑色粉末喷涂	PG29	
T1912100125-000	POWDER COATED,BLACK 粉末喷涂, 黑色	H10BPR-TSHC-M25	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,BLACK H10BPR上壳,中部锁定,侧出M25,黑色粉末喷涂	M25	
T1912100121-000	POWDER COATED,BLACK 粉末喷涂, 黑色	H10BPR-TSHC-PG21	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,BLACK H10BPR上壳,中部锁定,侧出PG21,黑色粉末喷涂	PG21	
T1912100120-000	POWDER COATED,BLACK 粉末喷涂, 黑色	H10BPR-TSHC-M20	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,BLACK H10BPR上壳,中部锁定,侧出M20,黑色粉末喷涂	M20	
T1912100116-000	POWDER COATED,BLACK 粉末喷涂, 黑色	H10BPR-TSHC-PG16	H10BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,BLACK H10BPR上壳,中部锁定,侧出PG16,黑色粉末喷涂	PG16	
PART NUMBER 料号	SURFACE TREATMENT 表面处理	PART DESCRIPTION 描述		PG/M THREAD-1 螺纹孔-1	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

-

DWN
Gino.Yao 10JUN2015

CHK
Chris.Wang 10JUN2015

APVD
Xiang.Xu 10JUN2015

PRODUCT SPEC
108-137014

APPLICATION SPEC
114-137014

WEIGHT
-

Customer Drawing

TE Connectivity

NAME
H10BPR-TSHC-PG/M

SIZE
A2

CAGE CODE
-

DRAWING NO
T191210XXXXX00

RESTRICTED TO
-

SCALE 1:1 SHEET 2 OF 2 REV B

1471-9 (3/13)