









TYPE B (DELPHI CLIP MOUNTING TYPE)
1-1743632-2



<TABLE 3>

TYPE B	TYPE A
1-1743632-2	0-1743632-2



3D EXPLODE VIEW
(SCALE 1:1)

<TABLE 1>

TYPE	PART NO.	WIRE SIZE(mm²)	Insulation DIA(mm)	Applicable WIRE	FINISH
MTII	0-962875-1	0.2~0.5	1.2~1.6	AVSSXF 0.5 Max	CuSn4
	0-962875-3				CuSn4(GOLD)
	0-962876-1	0.5~1.0	1.4~2.1	AVSSXF 0.85 Max	CuSn4
	0-962876-3				CuSn4(GOLD)
JPT	0-927770-3	0.5~1.0	2.0~2.7	FLK 1.0 Max	CuSn4
	2-927770-1				CuSn4(GOLD)
	0-927766-3	1.5~2.5	2.7~3.0	AVSS 2.0 Max or FLR 2.5 Max	CuSn4
	2-927766-1				CuSn4(GOLD)
MCP	1-968859-1	2.5~4.0	3.0~3.7	AEXF 3.0 Max or FLR 4.0 Max	CuNiSi

<TABLE 2>

TYPE	WIRE SIZE(mm²)	PART NO.	WIRE INSULATION DIAMETER(mm)	COLOR
MTII	0.35~0.5	964971-1	1.2~1.6	RED
	0.5~0.75	963530-1	1.4~1.9	GRAY
	1.0	964972-1	1.9~2.1	YELLOW
		963531-1	CAVITY PLUG	WHITE
JPT	0.35~1.0	828904-2	1.2~2.1	BLUE
	1.5~2.5	828905-1	2.2~3.0	WHITE
		828922-1	CAVITY PLUG	NATURAL
MCP	2.5~4.0	828985-1	3.0~3.7	GREEN
		828986-1	CAVITY PLUG	BROWN

NOTE

- GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
- DELIVERY CONDITION
- APPLIED CAP P/N: X-1743636-X
APPLIED WIRE COVER P/N: X-1743637-X
- APPLICABLE RECEPTACLE CONTACT P/N: TABLE 1
- APPLICABLE WIRE SEAL P/N: TABLE 2
- CLIP MOUNTING FEATURE : TABLE 3

4	INNER SEAL	SILICONE	RED ORANGE	I	I
3	LEVER	PBT-GF20	GRAY	I	I
2	MAIN PLUG (TYPE B)	PBT-GF15	BLACK	I	
	MAIN PLUG (TYPE A)	PBT-GF15	BLACK		I
1	FRONT PLUG	PBT-GF15	BLACK	I	I
NO	DESCRIPTION	MATERIAL	COLOR	O'TY	

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN
CHK
APVD
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

CH PARK
YM CHOI
JK SONG

SIZE
CAGE CODE
DRAWING NO
A1 00779

DRAWING NO
C=1743632

TE Connectivity

NAME
PLUG ASS'Y FOR
MTII JPT MCP SEALED 36P CONN'R

SIZE
CAGE CODE
DRAWING NO
A1 00779

RESTRICTED TO
-
REV
F

4805 (3/13)

4805 (3/13)